

# tiptel Ergophone 307

## User-friendly answering machine with excellent sound quality

After setting, three buttons are required to operate the Ergophone 307 quickly and completely. One key for "Message", one for "Next" and one for "Back". Deleting messages is not necessary because a buffer automatically deletes the oldest message as soon as the memory of 20 stored messages has been reached. In general, the answering machine has a storage capacity of 40 minutes. As usual with ergonomic Tiptel devices, the sound of the Ergophone 307 can be set very loud, the keys are extra-large, and the display font is easy to read.



### Highlights

#### tiptel Ergophone 307

- Ring buffer, messages do not have to be removed
- One message text, 20 records, recording capacity of 40 minutes
- Flash memory without batteries
- 4 keys for main functions
- 5 buttons for settings
- Easy to use with large buttons and sliders
- LED indicator for new messages
- Answer call optionally after 2, 5 or 7 rings
- Pause, repeat or skip the playback of messages at the touch of a button
- 2 connections (input and output), device can be connected between telephone connection and telephone
- Wall mounting possible

#### Tiptel b.v.

Camerastraat 2  
1322 BC Almere  
The Netherlands  
☎ +31 (0) 36 53 666 50  
☎ +31 (0) 36 53 678 81  
✉ info@tiptel.nl  
🌐 www.tiptel.nl

#### Tiptel NV

Imperiastraat 10/B8  
1930 Zaventem  
Belgium  
☎ +32 (0) 2 7149333  
☎ +32 (0) 2 7149334  
✉ info@tiptel.be  
🌐 www.tiptel.be